

SAUNDERS® Angle Seat Valves Engineered for high flow, rapid cycle hygienic applications



NEW!

MAXIMIZING VALVE LIFE IN EXCESS OF 3 M CYCLES

Applying our core engineering and design philosophy, SAUNDERS® Angle Seat Valves have been engineered to meet the exacting demands of process/utility applications across the spectrum of hygienic process industries.

1 LONGER SERVICE LIFE

Self aligning disk, multi layered spring loaded V Seals and polished stem interface ensure low friction operation and outstanding service life

2 MAINTENANCE FREE DESIGN

Highly engineered self adjusting packing system and self aligning seat eliminate need for routine maintenance saving significant operational cost and unplanned downtime

3 EFFICIENT OPERATION

360 degree actuator rotation permits ease of mounting, installation and operation







SAUNDERS® Angle Seat Valves

SELF ADJUSTING PACKING SYSTEM



Self adjusting spring loaded V seal packing gland system maintains constant pressure on stem packing ensuring a high integrity and secure sealing arrangement, trouble free operation and no unplanned maintenance.

360° HEAD ROTATION

Permits ease of installation mounting and operation. Removes possible exhaust air contamination and sedimentation of particles in operator crevices.



SELF ALIGNING SEAT



Self aligning seat ensures media containment and repeatable, maintenance free operation. Innovative design permits a flexible, controlled movement as the valve is closed to self adjust and align on the orifice seat. Sealing is 100% ensured.

Flow below seat (water hammer free) recommended for liquid media

LOW FRICTION OPERATION

Highly engineered interface between sealing system and polished spindle ensure low friction repeatable operation. In addition, the spindle is protected against possible contamination and damage by a contoured wiper ring. Low maintenance and extended lifetime ensured.



Materials of Construction

- Body Stainless Steel 316L Investment Cast CF3M ASTM A351 (DIN 1.4409)
- Seat, Seal: PTFE/NBR (Option PEEK/FKM)
- Actuator: Corrosion resistant glass filled nylon Grade PA66-GF33

Size Range

• DN 15-50 (0.5"-2.0")

Pressure Rating

Up to 25 bar

Temperature Range

- PTFE Seat -10 to 180°C (14 to 356°F)
- PEEK Seat for higher temperature up to 220°C (428°F)

Standard Features and Compliance

- PED / CE
- FDA compliant
- DIN 12266-1 leakage rate A (Air bubble tight closure)
- ANSI Class VI

Special Features

- Function: NC/NO/DA Bi Directional Operation
- Suitable up to 20mbar vacuum

Flow above seat,

recommended only

for gases and steam

• Fast Acting up to 1000 cycles/hour

Typical Applications

Ideally suited to high flow, rapid cycle, higher temperature applications:

INDUSTRIES

- Biotech
- Pharmaceutical
- Food
- Cosmetics
- Beverage
- Process/Utility Applications
- MEDIA
- Liquids
- Gases
- SteamAir
- Oils

Modular Accessories

Modular design options available to support process integration, such as:

- VUE intelligent position sensing
- · Stroke Limiter
- Positioners (Digital and Electro Pneumatic)
- Solenoid options according to global specification

CRANE CHEMPHARMA & ENERGY

Crane Process Flow Solutions Ltd. Grange Road Cwmbran, Gwent NP44 3XX United Kingdom Tel.: + 44-1633-486666 Crane Co., and its subsidiaries cannot accept responsibility for possible errors in catalogues, brochures, other printed materials, and website information. Crane Co. reserves the right to alter its products without notice, including products already on order provided that such alteration can be made without changes being necessary in specifications already agreed. All trademarks in this material are the property of the Crane Co. or its subsidiaries. The Crane and Crane brands logotype (CENTER LINE®, COMPAC-NOZ®, CRANE®, DEPA® & ELRO®, DOPAK®, DUO-CHEK®, FLOWSEAL®, GYROLOK®, GO REGULATOR®, HOKE®, JENKINS®, KROMBACH®, NOZ-CHEK®, PACIFIC VALVES®, RESISTOFLEX®, REVO®, SAUNDERS®, STOCKHAM®, TEXAS SAMPLING®, TRIANGLE®, UNI-CHEK®, VALVES®, WESTLOCK CONTROLS®, WTA®, and XOMOX®) are registered trademarks of Crane Co. All rights reserved.